

Unistat T305 HT

Heating Circulator for closed systems and open baths. Powerful - regulated - cooling, saves water, unpressurised. Stepper motor controlled HT cooler (High temperature cooler) and air-cooled heat exchanger. Closed circulation pump made of stainless steel with cooled shaft seal with free shaft, without bearing in the liquid. Automatical capacity adaption for heating. Expansion tank (not thermoregulated) for closed systems, lockable for open baths. Heat exchanger, moistened parts and housing made of stainless steel. With adjustable overtemperature protection according to DIN 12876.

Pilot ONF:

The new Pilot ONE controller with pioneering technology and advanced control functions brings numerous advantages to routine work. The extensive features list includes a brilliant 5,7" TFT touchscreen display, USB and network connections, an integrated technical glossary and language support in 13 languages (EN, DE, FR, IT, ES, RU, CN, PT, JP, CZ, PL, KO, TR). The Pilot ONE has a convenient navigation system with easily remembered icons and menu categories which are colour sorted to make routine work simpler. Thanks to a favourites menu and One-Click operator guidance all important information is always just a few keystrokes away. Software wizards also help you to set up, ensuring correct settings. The USB port allows connection of the system to a PC or notebook. Together with the Spy software, requirements such as remote control or data transmission are easily achieved in a cost-effective manner. Network integration is easy with the internet port.

further functions:

E-grade Professional installed as standard, TAC (True Adaptive Control) - self optimising internal and cascade control, selectable temperature control mode (Internal/Process), programmer with 10 programs (max. 100 steps), ramp function (linear and non-linear), 5 point calibration, scalable graphic display, favourites menu, display resolution 0,01 K, integrated technical glossary, 2nd set point, user menus (Administrator level), calendar start, wallpaper selection.

3-2-2 warranty - registration required.

Technical data according to DIN 12876

Operating temperature range Temperature stability at 70°C temperature set point / display

Resolution of display Internal temperature sensor

External sensor Interface digital

digital input
digital output
Alarm message
Safety classification
Heating power convertible
Cooling power at 300°C
Cooling power at 200°C
Cooling power at 100°C
Circulation pump:

max. delivery pressure Pump connection

max. permissible kin. viscosity

min. filling capacity

Filling capacity expansion tank
Overall dimensions WxDxH **

Net weight

sound pressure level +/- 4 dB(A)

Power supply convertible

max. current

max. current (3 Phase)
Fuse (1 phase)
Fuse (3 phase)
Degree of Protection
min. ambient temperature
max. ambient temperature

65... 300 °C 0.01 K

- -"

5,7" colour Touchscreen

0,01 K Pt100 Pt100

Ethernet, USB (Host u. Device), RS232

ECS ONE POKO ONE

optic, acoustic, relay Class III / FL

3,0kW or 6,0kW 3,2 kW

2,3 kW 0,6 kW

45 l/min 0.9 bar M24x1,5 male 50 mm²/s

1,9 I 2.8 I

425x250x631 mm

41 kg 54 dB(A)

230V 1~ 50/60Hz* or 400V 3~N 50/60Hz

14,5 A 10 A 16 A 3x10 A IP20 5 °C

40 °C



Order-No.: 1003.0020.01

from Serial-No.: 218993 1.0/15

Technical data according to DIN 12876

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Accessories and periphery: E-grade "Professional" #9496*, mini-USB cable *, E-grade "Explore" #10495, Com.G@te Namur, PC-Com.G@te-cabel, Holder for Com.G@te #10019, Com.G@te-extension cable: upon request, SpyLight-Software, Thermofluid, external pressure sensor, metal hoses, external sensor, connecting cable, float switch in sight glass for extended security.

Note: Pump connections: Bore shape Y (60°) according to DIN 3863, pipework/flexible tempering hoses: Ball socket according to DIN 3863, sleeve nut according to DIN 3870.

* standard equipment

Output data valid for: Room temperature 20°C

In accordance with EN60034-1 the following voltage and frequency tolerances are valid:

Voltage + / - 10%, as long as the frequency tolerance does not run in the opposite direction.

Example: -10% voltage and + 3% frequency -> not allowed!

-10% voltage and -3% frequency -> allowed.

Information to Electromagnetic compatibility: Classification (disturbance) to EN55011: Class A, Group 1

Alternative (factory set) power supply - please quote configuration at time of ordering.

** Please respect space requirements. See operating conditions at www.huber-online.com

Peter Huber Kältemaschinenbau AG Werner-von-Siemens-Str. 1 D-77656 Offenburg Tel 0781/9603-0 Fax 0781/57211 www.huber-online.com